



120 VAC 2 AMP CORD GRIP*

10 PIN CABLE CONNECTOR TO BSP-901

SPECIAL RELEASE 11-96

RS

SEE NOTE 1.

REF. HOFFMAN A-201612 LP BOX

22.50

21.25

LIGHT BEAM CENTER

LIGHT BEAM CENTER

9" top- 1" CLEARANCE

4" top- 1"

- * CAN BE REPLACED WITH CONDUIT FITTING.
4. AIR LINE FILTER SHOWN SHOULD BE MOUNTED IN A COOLER LOCATION FOR MORE EFFICIENT COOLING.
 3. AIR SUPPLY: 80-200 PSI, 25 SCFM min.
 2. DO NOT MOUNT DIRECTLY ON HOT SURFACES. USE SPACERS.
- NOTES: 1. WRAP AIR SUPPLY LINE IN HOT AREA WITH PIPE INSULATION.

IR HEAD ENCLOSURE, HI TEMP, with INTERNAL POWER SUPPLY & DUST SHIELD (INSTALLATION DRAWING)

MOISTURE REGISTER PRODUCTS
 Division of Aqua Measure Instrument Co.
 1712 EARHART CT, LaVerne, CA 91750

FILE NO.	551796-1
DATE	11-19-96
DRAWN BY	R. STRIEWSKI
APPROV. BY	<i>RS</i>
DWG. NO.	551796-1
SHEET	1 OF 1